

iEvac[®]

SMOKE/FIRE HOOD

The New Cost-Effective American-Certified Protection!

The iEvac[®] Protects against:

- **Carbon Monoxide**
- **Hydrogen Sulfide**
- **Additional Toxic Gases:** sarin, smoke, hydrogen cyanide, chlorine, ammonia, sulfur dioxide, tear gas, OC, and more
- **Harmful Particulates:** soot, fumes, aerosols, and others
 - Contains a HEPA P100 filter that removes sub-micron particles such as ebola, anthrax, ricin, smallpox, and radioactive particles
- **Life-Threatening Physical Hazards:** flammability and radiant heat



Qualified Anti-Terrorism Technology
U.S. Department of Homeland Security



Certified Model ASTM E2952



ElmridgeProtection.com • 561-244-8337 • info@ElmridgeProtection.com

Performance and Protection Capability Tests beyond the Requirements of American Standard ASTM E2952

Tested by US Army Research, Development and Engineering Command, Edgewood Chemical Biological Center

Function	Test Condition	Requirement	Result
Overall protection factor	Test subjects performing standard OSHA exercises inside the fit test chamber at Edgewood	2,000	> 90,000
Protection factor inside the hood but outside the nose cup	Test subjects performing standard OSHA exercises inside the fit test chamber at Edgewood	150	> 8,000

Physical Properties: Tested and Certified to American Standard ASTM E2952

Challenge	Test Condition	Duration	Result
Radiant heat	Within 9.5 inches (240 mm) of heating panel between 980 and 1700°F (527 and 927°C)	15 secs repeated	pass
Flammability	9.8 inches (250 mm) away from a burner flame of 1475°F (800°C)	One rotation	pass
Molten drip	Molten polypropylene rod drip	Each location	pass
Inhalation temperature	CO at 77°F (25°C) and 87%RH	15 mins	pass
Fogging	Read eye chart from 20 feet (6.1 meters) at the 20/100 line	5 mins	pass
Field of vision	Apertometer headform	viewing	pass
Light transmission	Haze of vision area	left and right	pass
Temperature variation	32°F (0°C) followed by 158°F (70°C)	24 hours each	pass
Pressure variation	Ambient to 4.4 psi (300 mbar) below	1,000 cycles	pass
Vibration	0.75 inches (19 mm) at 100 rpm	10,000 cycles	pass
Corrosion	Salt spray at 95°F (35°C) then 72°F (22°C) at 50% RH	48 hours each	pass
Puncture and tear	3.5 oz (100 grams) striker dropped from 4 inches (100 mm)	Ready to use	pass
Water leakage	Immerse in water at 160°F (70°C) to depth of 24 inches	5 mins	pass

Hood Performance Tests: Tested and Certified to American Standard ASTM E2952

Function	Test Condition	Duration	Requirement	Result
Speed of donning	Remove from pack and wear properly	Less than 30 secs	< 30 secs	pass
Total inward leakage	Test subjects performing standard exercises	2.5 mins	< 2%	<0.01%
Ocular leakage	Test subjects performing standard exercises	2.5 mins	< 20%	<0.1%
Carbon dioxide build-up	Breathing machine	25 cycles per min	< 2.5%	< 1.7%
Breathing resistance	Probed headform with breathing machine	30 cycles	-3.2 in (-81.5 mm) +1.2 in (+30.6 mm)	pass
Soot particulate	Inhalation breathing resistance with 200 mg/m ³ soot	5 mins	< 8 in (< 204 mm)	pass
Soot particulate	Exhalation breathing resistance with 200 mg/m ³ soot	5 mins	< 6 in (< 153 mm)	pass





TESTED BY



US Army Research, Development & Engineering Command
Edgewood Chemical Biological Center

Gas and Particulate Tests : Tested and Certified to American Standard ASTM E2952

Challenge	Symbol	Type	Concentration (ppm)	Requirement	Result
Carbon monoxide	CO	Hazardous combustion by-product	3,000	15 mins	> 45 mins
Carbon monoxide	CO	Hazardous combustion by-product	5,000	15 mins	> 46 mins
Hydrogen cyanide	HCN	Hazardous combustion by-product	400	15 mins	> 90 mins
Hydrogen chloride	HCl	Acid gas toxic industrial chemical	1,000	15 mins	> 70 mins
Sulfur dioxide	SO ₂	Acid gas toxic industrial chemical	100	15 mins	> 70 mins
Cyclohexane	C ₆ H ₁₂	Organic vapor toxic industrial chemical	500	15 mins	> 41 mins
Acrolein	C ₃ H ₄ O	Organic vapor toxic industrial chemical	100	15 mins	> 65 mins
Diethyl phthalate	DOP	Particulate aerosol 0.185 micron	200 mg/m ³	>95%	> 99.996%

Additional Gas and Particulate Tests

Challenge	Symbol	Type	Concentration (ppm)	Requirement	Result
Carbon monoxide	CO	Hazardous combustion by-product	10,000	15 mins	> 30 mins
Diethyl phthalate	DOP	HEPA filtration test for particulates and aerosols	200 mg/m ³	> 99.97%	> 99.996%
Ammonia	NH ₃	Toxic industrial gas	1,250	15 mins	> 60 mins
Formaldehyde	HCHO	Toxic industrial gas	250	15 mins	> 60 mins
Phosgene	COCl ₂	Toxic industrial gas	125	15 mins	> 60 mins
Phosphine	PH ₃	Toxic industrial gas	150	15 mins	> 60 mins
Chlorine	Cl ₂	Toxic industrial gas	200	15 mins	> 60 mins
DMMP	DMMP	Simulant for sarin nerve gas	1,000	15 mins	> 60 mins
Tear gas	CS	Tear gas	8	>8 hours	>8 hours
Tear gas	CN	Tear gas	16	>8 hours	>8 hours
Hydrogen sulfide	H ₂ S	Acid gas toxic industrial chemical	1,000	15 mins	> 600 mins
Hydrogen sulfide	H ₂ S	Acid gas toxic industrial chemical	5,000	15 mins	> 85 mins
Hydrogen sulfide	H ₂ S	Acid gas toxic industrial chemical	10,000	15 mins	> 40 mins
Hydrogen sulfide	H ₂ S	Acid gas toxic industrial chemical	20,000	15 mins	> 20 mins

Legal and trademark information. Copyright © 2015 Elmridge Protection Products, LLC. All rights reserved.

Certified to American Standard for Air-Purifying
Respiratory Protective Smoke Escape Devices ASTM E2952

iEvac[®]

SMOKE/FIRE HOOD



Certified Model ASTM E2952



- Maintenance-free
- At 9.5 in. (240mm) can withstand up to 1700°F (927°C) in radiant heat
- Twin filters for easier breathing
- Improved field of view compared with single filter in front
- Hood is a clear material resulting in an unobstructed field of view
- High visibility reflective strips for easy recognition
- Highest level of protection maintained by silicone neck dam
- Protects lungs, head, eyes, and face
- Can be used with eyeglasses, beards, and long hair
- Packaged in puncture- and- water-proof laminate barrier
- Quick and easy donning
- Latex-free
- One universal size

Weight of iEvac [®] in ready-to-use configuration:	1.4 lbs. – 635 grams
Size of iEvac [®] folded in vacuum-sealed foil bag:	Height – 5 ½ in (14 cm) Width – 5 ½ in (14 cm) Depth – 4 ¾ in (12 cm)
Shelf life:	5 ½ years from date of manufacture

For one-time use only. Read instructions before using.

- Ordering info:
- iEvac[®] Smoke/Fire Hood item # EBP-900
 - iEvac[®] Demo Hood item # EBP-200
 - iEvac[®] Nylon Carry-pouch item # EBP-270
 - iEvac[®] Single Wall-mounting Rack item # EBP-305
 - iEvac[®] Wall-mounting Cabinet EBP-312 w/ window and lock



iEvac[®] vacuum-sealed in foil bag



The iEvac[®] is listed on DHS's Authorized Equipment List & Standardized Equipment List



ElmridgeProtection.com

561-244-8337 • info@ElmridgeProtection.com

Distributed By: